



# Full Cycle Ratchet Hand Crimper, #26 AWG - #8 AWG, N Die

By Burndy  
Catalog # M8ND



Full Cycle Ratchet Hand Crimper, #26-#8 AWG.

## Features

- Fully protected ratchet mechanism
- Reinforced heavy duty back
- Long handles provide greater mechanical advantages
- Uses all standard BURNDY N-dies
- Easy groove identification with color-coded dies

## Application

Crimping

## General

Application - For Use On	#26-8 AWG Terminals and Splices
Die Type	N Die
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810029817
UPC 12 Digit	7818100298177

## Dimensions

Dimension - Length Overall inch	10.75 in
Dimension - Thread Size	-
Dimension - Width inch Length	1-3/4 in 10.75 in

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_082\\_OTOF\\_M8ND\\_lineart](#)  
[Sales Drawings - sd030323-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-M8ND-SPEC-EN | REV 5/2024