



# Manual Cable Cutter, up to 1000 kcmil Copper and Aluminum

By Burndy  
Catalog # [MCC1000](#)

Manual Cable Cutter, up to 1000 kcmil CU/AL.



## Features

- High quality design and construction
- Rugged high quality steel blades
- Fiberglass handles with soft grips

## Application

Cutting

## General

Application - For Use On	Aluminum, Copper Cable
Catalog Number	MCC1000
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Manual Cable Cutter
Type	Cutter
UPC	781810174869
UPC 12 Digit	7818101748699

## Dimensions

Cable Insulation Diameter Maximum	1.9 in
Length	32 in
Weight	9 lb
Width	6 in

## Conductor Related

Crimping Ranges	Cutting Capacity : Copper upto 1000 kcmil; Aluminum: upto 1000 kcmil
-----------------	--

## Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_MCC\\_CUTTER\\_LineArt](#)
- [Sales Drawings - SE211277-01\\_A](#)
- [Specifications - MCC1000](#)