



# Manual Cable Cutter, up to 600 kcmil Copper and Aluminum

By Burndy  
Catalog # [MCC600](#)

Manual Cable Cutter, up to 600 kcmil CU/AL.



## Features

- Rugged, high quality steel cutting blades
- Fiberglass handles with soft grips
- Excellent cutting edge performance
- Minimum of cable distortion

## Application

Cutting

## General

Application - For Use On	Aluminum, Copper Cable
Catalog Number	MCC600
Tool Type	Manual Cable Cutter
Type	Cutter
UPC	781810566114
UPC 12 Digit	7818105661144

## Dimensions

Cable Insulation Diameter Maximum	1.31 in
Length	21 in
Weight	3.5 lb

Width 5 in

## Conductor Related

Crimping Ranges Cutting Capacity : Copper upto 600 kcmil; Aluminum: upto 600 kcmil

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Minimum Pack Quantity 1  
Package Contents Tool only

## Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - Cutters](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50009950-01\\_B](#)  
[Specifications - MCC600](#)