



# HYTOOL™ Hand-Operated Crimper, O and D3 grooves; 24" Straight fiberglass handles

By Burndy  
Catalog # [MD612](#)



Crimper, O & D3 Grooves; 24" Straight Fiberglass Handles.

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD612
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
EU RoHS Indicator	Yes
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810446560
UPC 12 Digit	7818104465600

## Dimensions

Length	31.5 in
Weight	8.25 lb
Width	9.5 in

## Conductor Related

Crimping Ranges

Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

## Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_MD68\\_LA](#)
- [Sales Drawings - sd208717-01](#)
- [Specifications - MD612](#)