



HYTOOL™ Hand-Operated Crimper, J, M & P, T & X grooves

By Burndy
Catalog # [MD637](#)



Crimper, J, M & P, T & X Grooves.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD637
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810011027
UPC 12 Digit	7818100110277

Dimensions

Length	25.375 in
--------	-----------

Weight 6 lb

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_464750_MD6_MD66_MD637_MD638](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MD68_LA](#)
[Sales Drawings - sd206988-01](#)
[Specifications - MD637](#)