



HYTOOL™ Hand-Operated Crimper, Installs #14 - 4/0 AWG, Permanent D3 Groove

By Burndy
Catalog # [MD66](#)



Crimper, Installs #14-4/0 AWG, Permanent D3 Groove.

Application

Crimping

General

Application - For Use On Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors

Catalog Number	MD66
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
UPC	781810446102
UPC 12 Digit	7818104461022

Dimensions

Length	24.5 in
Width	6.65 in

Conductor Related

Crimping Ranges Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to

4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_464750_MD6_MD66_MD637_MD638](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MD68_LA](#)
[Sales Drawings - 50015859](#)
[Specifications - MD66](#)