



MD6 Hotstick Tool, Forged Steel Jaws BG & D3, 60" Fiberglass Pole

By Burndy
Catalog # [MD6HS60](#)



MD6 Hotstick Tool, BG & D3 Grooves, 60" Fiberglass Pole.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD6HS60
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
Tool Type	Hot Stick
Trade Name	HYTOOL™
Type	Crimper
UPC	781810446010
UPC 12 Digit	7818104460100

Dimensions

Length	69 in
Weight	15.5 lb

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MD6HS_LineArt](#)
[Sales Drawings - sa049180-01](#)
[Specifications - MD6HS60](#)



A Hubbell brand