



# MD6 Hotstick Tool, Forged Steel Jaws BG & D3, 72" Fiberglass Pole

By Burndy  
Catalog # [MD6HS72](#)



MD6 Hotstick Tool, BG & D3 Grooves, 72" Fiberglass Pole.

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD6HS72
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
Tool Type	Hot Stick
Trade Name	HYTOOL™
Type	Crimper
UPC	781810446126
UPC 12 Digit	7818104461266

## Dimensions

Length 80.06 in

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Minimum Pack Quantity 1  
Package Contents Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_MD6HS\\_LineArt](#)
- [Sales Drawings - 50005192](#)
- [Specifications - MD6HS72](#)



A Hubbell brand