



# HYTOOL™ Hand-Operated Crimper, Polymer Handles, O and D3 grooves; Carry case

By Burndy  
Catalog # [MD78WCS](#)



Crimper, Polymer Handles, O & D3 Grooves; Carry Case.

## Features

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD78WCS
Crimp Force Capacity	4.5 ton
Die Type	W and X Die
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
Type	Crimper
UPC	781810528846
UPC 12 Digit	7818105288466

## Dimensions

Length	25 in
Weight	7 lb
Width	8 in

## Conductor Related

Crimping Ranges	Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum
-----------------	---

## Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Metal Case

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30014719](#)
- [Specifications - MD78WCS](#)