



Full Cycle Ratchet Crimper, #22-10 AWG Vinyl Insulated Terminals and Splices

By Burndy
Catalog # [MR15](#)



Full Cycle Ratchet Crimper, #22-10 AWG Vinyl Insulated.

Features

- Permanent die sets
- Heavy duty forged steel frame
- Full cycle ratchet mechanism
- Emergency release
- Comfort grip handles

Application

Crimping

General

Application - For Use On	Vinyl Insulated Terminals and Splices
Catalog Number	MR15
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810011188
UPC 12 Digit	7818100111888

Dimensions

Dimensions	8.88 in x 6.00 in x 2.50 in
Height	2.5 in
Length	8.88 in
Weight	1.1 lb
Width	6 in

Conductor Related

Crimping Ranges #22 - #10 AWG

Certifications And Compliance

Buy American Compliant No
Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity 20
Minimum Pack Quantity 1
Package Contents Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Installation Manuals - MR15 MR18, MR20 Operating Manual](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_082_OTXF_MR15_MR18_MR20_lineart](#)
[Sales Drawings - 10113613](#)
[Specifications - MR15](#)