



Full Cycle Ratchet Crimper, #22-10 AWG Uninsulated (bare) Terminals and Splices

By Burndy
Catalog # [MR20](#)



Full Cycle Ratchet Crimper, #22-10 AWG Bare.

Features

- Permanent die sets
- Heavy duty forged steel frame
- Full cycle ratchet mechanism
- Emergency release
- Comfort grip handles

Application

Crimping

General

| | |
|--------------------------|-----------------------------------|
| Application - For Use On | Uninsulated Terminals and Splices |
| Catalog Number | MR20 |
| Die Type | Permanent Die Grooves |
| EU RoHS Indicator | Yes |
| Sub Brand | HYTOOL |
| Tool Type | Full Cycle Ratchet Crimper |
| Trade Name | HYTOOL™ |
| UPC | 781810011195 |
| UPC 12 Digit | 7818100111955 |

Dimensions

| | |
|------------|-----------------------------|
| Dimensions | 8.88 in x 6.00 in x 2.50 in |
| Height | 2.5 in |

| | |
|--------|---------|
| Length | 8.88 in |
| Weight | 1.1 lb |
| Width | 6 in |

Conductor Related

| | |
|-----------------|---------------|
| Crimping Ranges | #22 - #10 AWG |
|-----------------|---------------|

Certifications And Compliance

| | |
|------------------------------------|----|
| Buy American Compliant | No |
| Standards - RoHS Compliance Status | EX |

Logistics

| | |
|-----------------------|-----------|
| Carton Quantity | 20 |
| Minimum Pack Quantity | 1 |
| Package Contents | Tool only |

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Installation Manuals - MR15 MR18, MR20 Operating Manual](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_082_OTXF_MR15_MR18_MR20_lineart](#)
[Sales Drawings - 10113613](#)
[Specifications - MR20](#)