



Full Cycle Ratchet Crimper, #8-18 AN Copper #10-22 Sol, #8-22 Str

By Burndy
Catalog # [MR89Q](#)



Full Cycle Ratchet Crimper, #8-18 AN CU #10-22 Sol, #8-22 Str.

Features

- Long handles provide greater mechanical advantage
- Adjustable stop for terminals (lowers for splices)
- Color-coded die grooves
- Fully protected ratchet mechanism
- Reinforced heavy duty back
- High strength aluminum body

Application

Crimping

General

Application - For Use On	Uninsulated Terminals and Splices
Catalog Number	MR89Q
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810786031
UPC 12 Digit	7818107860311

Dimensions

Dimensions	11.00 in x 2.76 in x 0.88 in
------------	------------------------------

Height	0.88 in
Length	11 in
Weight	1.5 lb
Width	2.76 in

Conductor Related

Crimping Ranges	#18 - #8 AN, #22 - #8 AWG
-----------------	---------------------------

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MR8_LineArt](#)
- [Sales Drawings - sd041872-01](#)
- [Specifications - MR89Q](#)