



# Full Cycle Ratchet Crimper, Installs YEC180, YOE180, YEC200, YOE200 connectors, Test Wire: RG 59/U, RG 54A/U, Ground Wire: #20 AWG

By Burndy  
Catalog # [MR8EC4](#)



Full Cycle Ratchet Crimper, for YEC180, YOE180, YEC200, YOE200; Test Wire: RG 59/U, RG 54A/U; Ground Wire: #20 AWG.

## Features

- Fully enclosed, protected ratchet mechanism does not allow the handles to be opened until full ratchet cycle is completed
- Easy groove identification with color-coded dies
- Cast Aluminum body, other parts Alloy Steel

## Application

Crimping

## General

Catalog Number	MR8EC4
Die Type	Permanent Die Grooves
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810030011
UPC 12 Digit	7818100300111

## Dimensions

Dimensions	10.95 in x 2.00 in x 0.88 in
Height	0.88 in
Length	10.95 in
Width	2 in

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_MR8\\_LineArt](#)  
[Sales Drawings - SD037383-01](#)  
[Specifications - MR8EC4](#)