



Full Cycle Ratchet Crimper for Critical Applications, #22-10 AWG YAV, T, YAD connectors.

By Burndy
Catalog # [MR8G98](#)

Full Cycle Ratchet Crimper, Critical Applications, #22-10 AWG YAV, T, YAD connectors.



Features

- Long handles provide greater mechanical advantage
- Adjustable stop for terminals (lowers for splices)
- Color-coded die grooves
- Fully protected ratchet mechanism
- Reinforced heavy duty back
- High strength aluminum body

Application

Crimping

General

| | |
|--------------------------|-----------------------------------|
| Application - For Use On | Uninsulated Terminals and Splices |
| Die Type | Permanent Die Grooves |
| Tool Type | Full Cycle Ratchet Crimper |
| Trade Name | HYTOOL™ |
| Type | Crimper |
| UPC | 781810701072 |
| UPC 12 Digit | 7818107010722 |

Dimensions

| | |
|------------|------------------------------|
| Dimensions | 10.56 in x 3.31 in x 1.50 in |
| Height | 1.5 in |
| Length | 10.56 in |
| Weight | 1.5 lb |
| Width | 3.31 in |

Conductor Related

Crimping Ranges #22 - #10 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_MR8_LineArt](#)
[Sales Drawings - sd082682-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-MR8G98-SPEC-EN | REV 5/2024