



# Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Copper

By Burndy  
Catalog # [MRC840](#)

Crimper, #8-4/0 AWG CU.



## Features

- Spring loaded mechanism locks die wheel into position
- Press mechanism to release
- Rotating die wheel color coded marked with AWG sizes
- Steel jaws

## Application

Crimping

## General

Application - For Use On	Copper Terminals and Splices
Die Type	Rotating Die Wheel
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Mechanical Rotating Crimper
Trade Name	HYTOOL™
UPC	781810192504
UPC 12 Digit	7818101925044

## Dimensions

Dimensions	26.00 in x 8.00 in x 1.50 in
Height	1.50 in
Length	26.00 in
Weight	8.25 lb
Width	8.00 in

## Conductor Related

Crimping Ranges	Copper: #8 AWG- #4/0 AWG
-----------------	--------------------------

## Certifications and Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Installation Manuals - BUR\\_50097800\\_MRC840](#)  
[Sales Drawings - SE..211280-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-MRC840-SPEC-EN | REV 1/2024