



Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Copper

By Burndy
Catalog # [MRC840](#)

Crimper, #8-4/0 AWG CU.



Application

- Crimping

General

Application - For Use On	Copper Terminals and Splices
Die Type	Rotating Die Wheel
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Mechanical Rotating Crimper
Trade Name	HYTOOL™
UPC	781810192504
UPC 12 Digit	7818101925044

Dimensions

Dimensions	26.00 in x 8.00 in x 1.50 in
Height	1.5 in
Length	26 in
Weight	8.25 lb
Width	8 in

Conductor Related

Crimping Ranges	Copper: #8 AWG- #4/0 AWG
-----------------	--------------------------

Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - BUR_50097800_MRC840](#)
[Product Cross Section Image\(s\) - BUR_MRC840_lineart](#)
[Sales Drawings - SE..211280-01](#)



A proud member of the Hubbell Family.