



Ergonomic Full Cycle Ratchet Crimper, For use on #22-#10 Uninsulated (bare) Terminals and Splices



By Burndy
Catalog # [MRE1022B](#)

Full Cycle Ratchet Crimper, #22-#10 Bare.

Features

- Ratchet mechanism does not allow handles to open until full cycle is complete
- Stop plate ensures proper location for consistent reliable connection
- Die Inspection Gauges available (sold separately)
- Easy groove identification with color coded dies
- Ratchet release lever in case of misalignment

Application

Crimping

General

Application - For Use On	Uninsulated Terminals and Splices
Catalog Number	MRE1022B
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810512982
UPC 12 Digit	7818105129822

Dimensions

Dimensions	10.38 in x 3.00 in x 1.00 in
Height	1 in
Length	10.38 in
Weight	1.3 lb
Width	3 in

Conductor Related

Crimping Ranges Copper: #22 AWG - #10 AWG

Certifications And Compliance

Buy American Compliant No
Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_30009440_SOMI_MRE10-22B and MRE10-22NV](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MRE1022_lineart](#)
[Sales Drawings - 30013557](#)
[Specifications - MRE1022B](#)
[Video - Small Terminal Tools](#)