



Dieless Mechanical Crimper, Heavy Duty Forged Steel, #8 Str - 4/0 Str Copper Aircraft Cable

By Burndy
Catalog # [MY28](#)

Dieless Crimper, #8 Str-4/0 Str CU Aircraft Cable.



Features

- Easy to adjust nest die with knurled steel knob and machine heads
- Rugged tool design with heavy duty forged steel with reinforced back and handles
- Bench mount adapter (sold separately) available
- 31" diameter hole for bench mounting operations

Application

Crimping

General

Application - For Use On	#8-4/0 AWG Copper Aircraft Cable (YAV-L, YSV-L)
Catalog Number	MY28
Die Type	Dieless
EU RoHS Indicator	Yes
Finish Type	Black Matte
Sub Brand	HYTOOL
Tool Type	Mechanical Dieless Crimper
Trade Name	HYTOOL™
UPC	781810461952
UPC 12 Digit	7818104619522

Dimensions

Dimensions	22.65 in x 4.86 in x 1.12 in
Height	1.12 in
Length	22.65 in
Weight	8 lb
Width	4.86 in

Conductor Related

Crimping Ranges	#8 Str. - 4/0 Str.
-----------------	--------------------

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MY_LineArt](#)
[Sales Drawings - sd026316-01](#)
[Specifications - MY28](#)



A Hubbell brand