



Dieless Mechanical Crimper, Heavy Duty Forged Steel, #8 Str - 4/0 Str Aluminum Aircraft Cable

By Burndy
Catalog # [MY284](#)

Dieless Crimper, #8 Str-4/0 Str AL Aircraft Cable.



Features

- Two-ply covered handles of MY29-3C and MY29-11C designs
- Heavy duty forged steel back body and handles
- Strong reinforced forged steel back
- Setting plate
- .31" diameter hole for bench mounting operations
- Comfort grips
- Extra strong heavy duty reinforced handles
- Indentor die
- Knurled steel adjusting knob

Application

Crimping

General

Application - For Use On	#8-4/0 AWG Aluminum Aircraft Cable (YAV-A-L, YSV-A-L, YAV-A-R)
Die Type	Dieless
Finish Type	Black Matte
Tool Type	Mechanical Dieless Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810461969
UPC 12 Digit	7818104619699

Dimensions

Dimensions	22.65 in x 4.86 in x 1.12 in
Height	1.12 in
Length	22.65 in
Weight	8 lb
Width	4.86 in

Conductor Related

Crimping Ranges	#8 Str. - 4/0 Str.
-----------------	--------------------

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_MY_LineArt](#)
[Sales Drawings - sd026316-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-MY284-SPEC-EN | REV 5/2024