



Dieless Mechanical Crimper, #8 Str - 250 kcmil Copper Code, #8 Str - 4/0 Str Copper Flex, 30 Navy - 250 Navy Copper Navy Cable

By Burndy
Catalog # MY2911



Dieless Crimper, #8 Str-250 kcmil CU Code, #8 Str-4/0 Str CU Flex, 30-250 Navy CU Navy Cable

Application

Crimping

General

Application - For Use On	#8-250 kcmil CU Code, 30 Navy-250 Navy CU Navy Cable, #8-4/0 Flex CU Mine Machine Cable
Catalog Number	MY2911
Die Type	Dieless
EU RoHS Indicator	Yes
Finish Type	Black Matte
Sub Brand	HYTOOL
Tool Type	Mechanical Dieless Crimper
Trade Name	HYTOOL™
UPC	781810462201
UPC 12 Digit	7818104622011

Dimensions

Dimensions	22.65 in x 4.86 in x 1.12 in
Height	1.12 in
Length	22.65 in
Weight	8 lb
Width	4.86 in

Conductor Related

Crimping Ranges	#8 Str. - 250 kcmil, 30 Navy - 250 Navy, #8 Str. - 4/0 Str
-----------------	--

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MY_LineArt](#)
- [Sales Drawings - sd026316-01](#)
- [Specifications - MY2911](#)