



Dieless Mechanical Crimper, Covered Handles, #8 Str - 250 kcmil Copper Code, #8 Str - 4/0 Str Aluminum Code, 30 Navy - 250 Navy Copper Navy Cable

By Burndy
Catalog # [MY293C](#)



Dieless Crimper, Covered Handles.

Application

Crimping

General

Application - For Use On	#8-250 kcmil CU Code, 30 Navy-250 Navy CU Navy Cable, #8-4/0 AL Code
Catalog Number	MY293C
Die Type	Dieless
EU RoHS Indicator	Yes
Finish Type	Black Matte
Tool Type	Mechanical Dieless Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810462102
UPC 12 Digit	7818104621022

Dimensions

Dimensions	22.65 in x 4.86 in x 1.12 in
Height	1.12 in
Length	22.65 in
Weight	8 lb
Width	4.86 in

Conductor Related

Crimping Ranges	#8 Str. - 250 kcmil, 30 Navy - 250 Navy, #8 Str. - 4/0 Str
-----------------	--

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MY_LineArt](#)
- [Sales Drawings - sd026316-01](#)
- [Specifications - MY293C](#)