

## Substation - Copper Stud Connector

By Burndy

Catalog # [N11DR6644T12](#)

Copper Stud Connectors.



### Application

Substation

### General

Catalog Number	N11DR6644T12
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Tap Conductors	2
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810176597
UPC 12 Digit	7818101765977

### Dimensions

Dimension - AA Pad Orientation	90 Degree; In-line
Dimension - Pin Diameter fraction	1-1/4 in
Dimension - Pin Diameter inch	1.25 in
Dimension - Threads per inch	12

### Conductor Related

Conductor - Connection Combination	Stud to Tube
Conductor - Copper Solid Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2 AWG-4/0 AWG

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
-----------------------------	---

Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Tube Std Size	3/8 IPS IPS;1/2 IPS IPS;3/4 IPS IPS
Conductor - Copper Tube Std Size Range	3/8 IPS IPS-3/4 IPS IPS

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	2
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sd037349](#)  
[Specifications - N11DR6644T12](#)