

NHNT3434, Substation Copper T Connector, 90 Degrees, Cable to Cable, 1/0 Sol-500 kcmil

By Burndy

Catalog # [NHNT3434](#)



Cast Copper alloy T-Connector, 1/0 Sol.-500 kcmil, 4.84 in Length, Cable to Cable.

Application

Substation

General

Catalog Number	NHNT3434
Connector Type	T-Connector
EU RoHS Indicator	Yes
Installation Torque	480 lb-in
Recommended in-lb	
Material	Copper Alloy, Cast
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Sub Brand	T-CONNECTOR
Type	Tube to Cable Couplers
UPC	781810002230
UPC 12 Digit	7818100022300

Dimensions

Dimension - B Length fraction	2-31/50 in
Dimension - B Length inch	2.62 in
Dimension - Height fraction	2-8/25 in
Dimension - Height inch	2.32 in
Dimension - Height mm	58.9 mm
Dimension - L Length Overall mm	137 mm
Dimension - Length BB inch	2.62 in
Dimension - Length Overall inch	5.38 in
Dimension - Width fraction	2-14/25 in
Dimension - Width inch	2.56 in
Dimension - Width mm	65 mm

Conductor Related

Conductor - Connection Combination	Cable to Cable
------------------------------------	----------------

Conductor - Copper Solid Run Range	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Run Range	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	1/0 -500 kcmil
Conductor - Copper Str Tap Range	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	1/0 -500 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Run • CU C Str-Run • CU C Solid-Run • CU C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - NHNT3434_MODEL-PDF](#)
[3D Models - NHNT3434_MODEL-STEP](#)
[3D Models - NHNT3434_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

