



NYFTH4634CCP, Copper - T-Tap Limiter

By Burndy
Catalog # [NYFTH4634CCP](#)

High Capacity Limiter T-Connector for 1500 KCMIL (1.412 DIA) RUN and 500 KCMIL (.814 DIA) TAP, Max Voltage = 600 volts.



Application

Underground

General

Die Index 20
UPC 621945463943

Dimensions

Height 4.5 in
Length 16.78 in

Conductor Related

Conductor - Copper Str Run 1500 Kcmil
Conductor - Copper Str Tap 500 Kcmil

Logistics

Carton Quantity 3
Minimum Pack Quantity 3
Pallet Quantity 96

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50069808](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-NYFTH4634CCP-SPEC-EN | REV 5/2024