



Full Cycle Ratchet Crimper, Dieless, 6000 lbs, Installs Service Entrance Splice Connectors #10 AWG - #1/0 AWG

By Burndy
Catalog # OH25



Full Cycle Ratchet Crimper, Dieless, Service Entrance.

Features

- Heat treated steel
- 1/4" hole for snap fastener
- Forged steel jaws
- Nest die
- Comfort grip handles
- Spring loaded handles
- Protected ratchet mechanism
- Replacement stainless steel indentor

Application

- Crimping

General

Application - For Use On	Service Entrance Splices
Catalog Number	OH25
Die Type	Dieless
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper, Dieless
Trade Name	HYTOOL™
UPC	781810452004
UPC 12 Digit	7818104520044

Dimensions

Dimensions	12.00 in x 0.75 in x 6.25 in
Height	6.25 in
Length	12 in
Weight	2.687 lb
Width	0.75 in

Conductor Related

Crimping Ranges	Aluminum: #10 AWG - #1/0 AWG
-----------------	------------------------------

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance	EX
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_082_OT8F_OH25_lineart](#)
- [Sales Drawings - 210780](#)
- [Specifications - OH25](#)