



PENETROX Bottle 8 Ounce

By Burndy
Catalog # P8A

Penetrox Bottle, 5.80 in Length, 2.04 in Width



Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

General

Application - For Use On	Aluminum to Aluminum; Aluminum to Conduit; Aluminum to Copper
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592557
UPC 12 Digit	7818105925577
Viscosity at 100 Fahrenheit	305 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	8 oz
Minimum Pack Quantity	1

Product Assets

- [3D Models - P8A_MODEL-IGES](#)
- [3D Models - P8A_MODEL-STEP](#)
- [3D Models - P8A_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - SC087702-01](#)
- [SDS - PENETROX A ESPANOL SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A FRENCH SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A ESTONIAN SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A SDS \(GHS\) \(2019-07\)](#)
- [SDS - PENETROX A PORTUGUESE SDS \(GHS\) \(2019-07\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-P8A-SPEC-EN | REV 1/2024