



PATRIOT® PAT221 Small Terminal Battery Crimper, (2) Die Wheels for #12 AWG-#1 AWG, (2) 2.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT221D02A2](#)



PAT221 Small Terminal Battery Crimper, (2) Die Wheels for #12 AWG-#1 AWG, 2Ah Li-ion, AC, Hard Case

Features

- Dies Included: (2) Die Wheels: 81WHL221, 122WHL221
- Scissor action head design
- One-second cycle time with auto retract and calibration
- Interchangeable crimping dies and wheels
- Connector hold feature for easy wire insertion
- LED Worklight
- Red LED to indicate an incomplete crimp
- Safety Trigger Lock and Emergency Release

Application

Crimping

General

Application - For Use On	Copper Terminals, Splices
Battery Type	2.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT221D02A2
Container Type	Hard Case
Die Type	Interchangeable
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945665552
UPC 12 Digit	621945665552

Dimensions

Dimensions	10.6 in x 2.8 in x 4.2 in
Height	4.2 in
Length	10.6 in
Weight	2.6 lb
Width	2.8 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #22 AWG - #1 AWG terminals and splices
-----------------	--

Certifications And Compliance

Buy American Compliant	No
------------------------	----

Logistics

Package Contents	Crimper, (2) Die Wheels: 81WHL221, 122WHL221, (2) 2.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case
------------------	--

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - 50121182 - PAT221 Safety Operating & Maintenance Instructions \(SOMI\)](#)
[Sales Drawings - Sales Drawing 50124041](#)
[SDS - Lithium-Ion Rechargeable Battery Pack BL1820B](#)