



PATRIOT® 11-Ton Dieless C-Head Battery Crimper, (2) 5.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # [PAT444SL5DC](#)



PAT444S 11T Dieless C-Head Battery Crimper, 5Ah Li-ion, DC, Hard Case.

Features

- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum, #4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Head Rotation
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Contact Manufacturer
Power Source	12V-DC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945484344
UPC 12 Digit	621945484344

Dimensions

Dimensions	3.2 in x 13.7 in x 16.9 in
Height	16.9 in
Length	3.2 in
Weight	14.80 lb
Width	13.7 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_PAT444S_trilingual](#)
- [Sales Drawings - 50076051](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Video - The New PAT444S Dieless Tool](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PAT444SL5DC-SPEC-EN | REV 1/2024