



PATRIOT® 11-Ton Dieless C-Head Battery Crimper, No Batteries, No Charger, Hard Case

By Burndy
Catalog # [PAT444SLCB](#)



PAT444S 11T Dieless C-Head Battery Crimper, No Batteries, No Charger, Hard Case.

Features

- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Head Rotation
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT444SLCB
Container Type	Hard Case
Crimp Force Capacity	11 ton
Die Type	Dieless
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945524873
UPC 12 Digit	621945524873

Dimensions

Dimensions	3.2 in x 13.7 in x 16.9 in
Height	16.9 in
Length	3.2 in
Weight	14.8 lb
Width	13.7 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Hard Case

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_PAT444S_trilingual](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50076051](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT444SLCB](#)