



PATRIOT® 11-Ton Dieless C-Head Battery Crimper, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # PAT444SLI



PAT444S 11T Dieless C-Head Battery Crimper, 3Ah Li-ion, AC, Hard Case.

Features

- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Head Rotation
- Ergonomically balanced

Application

- Crimping

General

| | |
|--------------------------|--|
| Application - For Use On | Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads |
| Battery Type | 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries) |
| Catalog Number | PAT444SLI |
| Container Type | Hard Case |
| Crimp Force Capacity | 11 ton |
| Die Type | Dieless |
| EU RoHS Indicator | Contact Manufacturer |
| Power Source | 120V-AC Charger |
| Recharge Time | 0.5 h |
| Sub Brand | PATRIOT® CRIMPER |
| Tool Type | Battery Actuated Crimper |
| Trade Name | PATRIOT® |
| Type | <ul style="list-style-type: none">• Crimper• Sertisseur |
| UPC | 621945474451 |
| UPC 12 Digit | 621945474451 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 16.90 in x 3.20 in x 13.70 in |
| Height | 13.7 in |
| Length | 16.9 in |
| Weight | 14.8 lb |
| Width | 3.2 in |

Electrical Ratings

| | |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

Conductor Related

| | |
|-----------------|---|
| Crimping Ranges | Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil |
|-----------------|---|

Logistics

| | |
|-----------------------|--|
| Minimum Pack Quantity | 1 |
| Package Contents | Crimper, (2) Batteries, Charger, Lanyard, Hard Case |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_PAT444S_trilingual](#)
[Sales Drawings - 50076051](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Video - The New PAT444S Dieless Tool](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PAT444SLI-SPEC-EN | REV 6/2024