



PATRIOT® T3 Technology 11-Ton Dieless Battery Crimper, C-Head, Uncovered, (2) 3.0Ah 18V Li-Ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy
Catalog # [PAT444ST3U03A3](#)



PAT444ST3 Tech 11T Dieless Battery Crimper, C-Head, Uncovered, 3Ah Li-Ion, AC, Nylon Pro Bag

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments, photos, and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Nylon Pro Bag
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Tool Type	Battery
Type	Crimper
UPC	621945625129

Dimensions

Dimensions	14.95 in x 3.25 in x 16.9 in
Height	16.9 in
Length	14.95 in
Weight	15.20 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	--

Logistics

Carton Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_PAT444S_trilingual](#)
- [Sales Drawings - 50108199](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Video - BURNDY T3 APP Features and Benefits](#)
- [Video - BURNDY T3 APP Install & Register](#)
- [Video - Introducing the PAT444ST3](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PAT444ST3U03A3-SPEC-EN | REV 1/2024