



**PATRIOT® T3 Technology 11-Ton
Dieless Battery Crimper, C-Head,
Uncovered, (2) 5.0Ah 18V Li-Ion
Batteries, 12V-DC Charger, Nylon
Pro Bag**

By Burndy
Catalog # [PAT444ST3U05D3](#)



PAT444ST3 Tech 11T Dieless Battery Crimper, C-Head,
Uncovered, 5Ah Li-Ion, DC, Nylon Pro Bag.

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments, photos, and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-Head for easy access and increased flexibility
- Dieless System with range taking capability
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Nylon Pro Bag
Crimp Force Capacity	11 ton
Die Type	Dieless
Power Source	12V-DC Charger
Tool Type	Battery
Type	Crimper
UPC	621945625150

Dimensions

Dimensions	14.95 in x 3.25 in x 16.9 in
Height	16.9 in
Length	14.95 in
Weight	15.2 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Logistics

Carton Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_PAT444S_trilingual](#)
[Sales Drawings - 50108199](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Video - BURNDY T3 APP Install & Register](#)
[Video - Introducing the PAT444ST3](#)
[Video - BURNDY T3 APP Features and Benefits](#)



A proud member of the Hubbell Family.