



## PATRIOT® 15-Ton Covered C-Head Battery Actuated Crimper, Hydraulic Self-Contained, No Batteries, No Charger, Nylon Pro Bag



By Burndy  
Catalog # [PAT46CLWSLILCBPB](#)

PAT46 15T Covered C-Head Battery Crimper, No Batteries, No Charger, Nylon Pro Bag.

### Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Ergonomically balanced

### Application

Crimping

### General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46CLWSLILCBPB
Container Type	Nylon Pro Bag
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Contact Manufacturer
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561687
UPC 12 Digit	621945561687

### Dimensions

Dimensions	18.44 in x 3.26 in x 12.88 in
Height	12.88 in
Jaw Width	2.00 in
Length	18.44 in
Weight	18.95 lb
Width	3.26 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Nylon Pro Bag
Pallet Quantity	12

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50106125](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)  
[Specifications - PAT46CLWSLILCBPB](#)



A Hubbell brand