



# PATRIOT® 15-Ton Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, No Batteries, No Charger, Hard Case



By Burndy  
Catalog # PAT46LWLILCB

PAT46 15T Latch Head Battery Crimper, No Batteries, No Charger, Hard Case.

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46LWLILCB
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810654798
UPC 12 Digit	7818106547988

## Dimensions

Dimensions	18.59 in x 3.26 in x 13.93 in
Height	13.93 in
Jaw Width	2.00 in
Length	18.59 in
Weight	15.5 lb
Width	3.26 in

## Electrical Ratings

Operating Voltage 18 VDC

## Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

## Certifications And Compliance

Standards - RoHS Compliance UI Status

## Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Hard Case

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50002858](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT46LWLILCB](#)