



# PATRIOT® 15-Ton C-Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 5.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy  
Catalog # [PAT46LWSL5DC](#)



PAT46 15T C-Head Battery Crimper, 5Ah Li-ion, DC, Hard Case.

## Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Ergonomically balanced

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Power Source	12V-DC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945470071
UPC 12 Digit	621945470071

## Dimensions

Dimensions	18.44 in x 3.26 in x 12.88 in
Height	12.88 in
Jaw Width	2.00 in
Length	18.44 in
Weight	17.65 lb
Width	3.26 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

## Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50067989](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-PAT46LWSL5DC-SPEC-EN | REV 1/2024