



PATRIOT® 4-POINT® 6-Ton Dieless C-Head Battery Actuated Crimper, Hard Case, No Batteries or Charger

By Burndy

Catalog # [PAT4PC834LILCB](#)



PAT4PC834 4-POINT® 6T Dieless C-Head Battery Crimper, Hard Case, No Batteries or Charger.

Features

- Dieless System with range taking capabilities
- 360° head rotation
- 1.06" Jaw opening
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT4PC834LILCB
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	Dieless
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC	781810540954
UPC 12 Digit	7818105409544

Dimensions

Dimensions	15.62 in x 3.25 in x 14.10 in
Height	14.1 in
Length	15.62 in
Weight	12.5 lb
Width	3.25 in

Conductor Related

Crimping Ranges	Copper Terminals: #8-1000 kcmil Copper Splices: #8-500 kcmil Copper Flex Terminals: #8-777.7 Flex Copper Flex Splices: #8-500 kcmil Aluminum Terminals: #8-750 kcmil Aluminum Splices: #8-350 kcmil*
	*1.06" barrel diameter maximum for aluminum splices due to jaw opening Aluminum HYPLUG™: #8-750 kcmil

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Hard Case

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT4PC834LILCB](#)

