



PATRIOT® 4-POINT® 6-Ton Dieless C-Head Battery Actuated Crimper, No Batteries, No Charger, Nylon Pro Bag



By Burndy
Catalog # [PAT4PC834LILCBPB](#)

PAT4PC834 4-POINT® 6T Dieless C-Head Battery Crimper, No Batteries, No Charger, Nylon Pro Bag.

Features

- Dieless System with range taking capabilities
- 360° head rotation
- 1.06" Jaw opening
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT4PC834LILCBPB
Container Type	Nylon Pro Bag
Crimp Force Capacity	6 ton
Die Type	Dieless
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC	621945561960
UPC 12 Digit	621945561960

Dimensions

Dimensions	15.62 in x 3.25 in x 14.10 in
Height	14.1 in
Length	15.62 in
Weight	12.5 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges

Copper Terminals: #8-1000 kcmil
 Copper Splices: #8-500 kcmil
 Copper Flex Terminals: #8-777.7 Flex
 Copper Flex Splices: #8-500 kcmil
 Aluminum Terminals: #8-750 kcmil
 Aluminum Splices: #8-350 kcmil*
 *1.06" barrel diameter maximum for aluminum splices due to jaw opening
 Aluminum HYPLUG™: #8-750 kcmil

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Crimper, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50106125](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT4PC834LILCBPB](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-PAT4PC834LILCBPB-SPEC-EN | REV 10/2024