



PATRIOT® 6-Ton Scissor Action, O/D3 Crimp Jaw, No Batteries, No Charger, Hard Case

By Burndy

Catalog # [PAT500SJ68LILCB](#)



PAT500SJ 6T Scissor Action, O/D3 Crimp Jaw, Hard Case, No Batteries or Charger.

Features

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

Application

Crimping and Cutting

General

Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT500SJ68LILCB
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Power Source	No Charger
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT®
Type	Crimper and Cutter
UPC	781810673881
UPC 12 Digit	7818106738811

Dimensions

Dimension - Height mm	340.4 mm
Dimensions	16.80 in x 2.90 in x 13.40 in
Height	13.4 in
Length	16.8 in
Weight	10.1 lb
Width	2.9 in

Conductor Related

Crimping Ranges	Copper: #10 sol. - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; Aluminum: #14 sol. - 350 kcmil; ACSR: #14 sol. - 4/0 AWG
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, O/D3 Crimp Jaw, Lanyard, Hard Case

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50024949](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT500SJ68LILCB](#)