



PATRIOT® 6-Ton Scissor Action, BG/D3 Crimp Jaw, (2) 5.0Ah 18V Li-ion Batteries, 12V-DC Charger, Hard Case

By Burndy
Catalog # PAT500SJ6L5DC



PAT500SJ 6T Scissor Action, BG/D3 Crimp Jaw, 5Ah Li-ion, DC, Hard Case.

Features

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

Application

Crimping and Cutting

General

Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Power Source	12V-DC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT®
Type	Crimper and Cutter
UPC	621945470736
UPC 12 Digit	621945470736

Dimensions

Dimensions	16.80 in x 2.90 in x 13.40 in
Height	13.40 in
Length	16.80 in
Weight	10.10 lb
Width	2.90 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #10 sol. - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; Aluminum: #14 sol. - 350 kcmil; ACSR: #14 sol. - 4/0 AWG
-----------------	---

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, BG/D3 Crimp Jaw, (2) Batteries, Charger, Lanyard, Hard Case

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50068040](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.