



**PATRIOT® 6-Ton Scissor Action,  
BG/D3 Crimp Jaw, ACSR Cut Jaw,  
(2) 3.0Ah 18V Li-ion Batteries,  
120V-AC Charger, Hard Case**

By Burndy  
Catalog # [PAT500SJ6LICUTKIT1](#)



PAT500SJ 6T Scissor Action, BG/D3 Crimp Jaw, ACSR Cut Jaw, 3Ah Li-ion, AC, Hard Case.

**Features**

- Interchangeable scissor action crimping and cutting jaws available
- 180° Head rotation
- Pistol style body
- Uses W and X dies
- Ergonomically balanced

**Application**

Crimping and Cutting

**General**

Application - For Use On	Overhead Full Tension Deadends, Full Tension Splices and Terminals, Stirrups, Splices, Taps, and Terminals
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Power Source	12V-DC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Scissor Action
Trade Name	PATRIOT®
Type	Crimper and Cutter
UPC	621945437289
UPC 12 Digit	6219454372899

**Dimensions**

Dimensions	16.80 in x 2.90 in x 13.40 in
Height	13.4 in
Length	16.8 in
Weight	10.1 lb
Width	2.9 in

**Electrical Ratings**

Operating Voltage	18 VDC
-------------------	--------

**Conductor Related**

Crimping Ranges	Copper: #10 sol. - 500 kcmil;Copper Flex: #8 AWG - 350 kcmil;Aluminum: #14 sol. - 350 kcmil;ACSR: #14 sol. - 4/0 AWG
-----------------	--

**Certifications And Compliance**

Standards - RoHS Compliance	UI
Status	

**Logistics**

Minimum Pack Quantity	1
Package Contents	Tool, BG/D3 Crimp Jaw, ACSR Cut Jaw, (2) Batteries, Charger, Lanyard, Hard Case

**Product Assets**

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50024949](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

