



# PATRIOT® 6-Ton Covered Latch Head Battery Actuated Crimper, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy  
Catalog # PAT600CLI



PAT600 6T Covered Latch Head Battery Crimper, 3Ah Li-ion, AC, Hard Case.

## Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT600CLI
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810512913
UPC 12 Digit	7818105129133

## Dimensions

Dimension - Height mm 0 mm

Dimensions	14.50 in x 3.50 in x 13.75 in
Height	13.75 in
Length	14.5 in
Weight	9 lb
Width	3.5 in

## Electrical Ratings

Operating Voltage 18 VDC

## Conductor Related

Crimping Ranges Copper: #8 AWG - 600 kcmil; Copper Flex: #8 AWG - 350 kcmil; Aluminum: #8 AWG - 350 kcmil

## Certifications And Compliance

Standards - RoHS Compliance EX Status

## Logistics

Minimum Pack Quantity 1  
Package Contents Crimper, (2) Batteries, Charger, Lanyard, Hard Case

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30001989](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)  
[Specifications - PAT600CLI](#)