



PATRIOT® 6-Ton Latch Head Battery Crimper, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy
Catalog # [PAT600L5PB](#)



PAT600 6T Latch Head Battery Crimper, 5Ah Li-ion, AC, Nylon Pro Bag.

Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum Terminals and Splices
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT600L5PB
Container Type	Nylon Pro Bag
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561519
UPC 12 Digit	621945561519

Dimensions

Dimensions	14.50 in x 3.50 in x 13.75 in
Height	13.75 in

Length	14.5 in
Weight	8.65 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG - 600 kcmil; Copper Flex: #8 AWG - 350 kcmil; Aluminum: #8 AWG - 350 kcmil
-----------------	--

Certifications And Compliance

Buy American Compliant	No
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50106125](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT600L5PB](#)