



PATRIOT® 6-Ton Covered Latch Head Battery Actuated Crimper, (2) 3.0Ah 18V Li-ion Batteries, No Charger, No Case

By Burndy
Catalog # PAT600LILCC



PAT600 6T Latch Head Battery Crimper, 3Ah Li-ion, No Charger or Case.

Features

- Specialized latch head design with 180° rotation
- Permanent D3 crimp groove accepts all W Dies
- High speed pump completes crimp in approximately 3 seconds
- Enhanced clearance for tap connections
- Ergonomically balanced

Application

Crimping

General

| | |
|--------------------------|--|
| Application - For Use On | Copper, Aluminum Terminals and Splices |
| Battery Type | 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries) |
| Catalog Number | PAT600LILCC |
| Container Type | No Case/Bag |
| Crimp Force Capacity | 6 ton |
| Die Type | W Die and X Die |
| Power Source | No Charger |
| Recharge Time | 0.5 h |
| Tool Type | Battery Actuated Crimper |
| Trade Name | PATRIOT® |
| Type | Crimper |
| UPC | 781810650974 |
| UPC 12 Digit | 7818106509744 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 14.50 in x 3.50 in x 13.75 in |
| Height | 13.75 in |
| Length | 14.5 in |
| Weight | 8.65 lb |
| Width | 3.5 in |

Conductor Related

| | |
|-----------------|--|
| Crimping Ranges | Copper: #8 AWG - 600 kcmil; Copper Flex: #8 AWG - 350 kcmil; Aluminum: #8 AWG - 350 kcmil |
|-----------------|--|

Certifications And Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | UI |
|------------------------------------|----|

Logistics

| | |
|-----------------------|---------------------------------|
| Minimum Pack Quantity | 1 |
| Package Contents | Crimper, (2) Batteries, Lanyard |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT600LILCC](#)