



PATRIOT® 11-Ton Dieless Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # PAT644L5



PAT644 11T Dieless Latch Head Battery Crimper, 5Ah Li-ion, AC, Hard Case.

Features

- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum, #4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Rotatable latch head
- Audible pop-off indicates properly completed crimps
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.75 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945470972
UPC 12 Digit	621945470972

Dimensions

Dimensions	15.60 in x 3.20 in x 14.10 in
Height	14.10 in
Length	15.60 in
Weight	14.55 lb
Width	3.20 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 kcmil; Copper Flex: #2 AWG - 777 kcmil; Aluminum: #6 AWG - 900 kcmil; ACSR #4 AWG - 556.5 kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50068008](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.