



PATRIOT® 11-Ton Dieless Latch Head Battery Crimper, No Batteries, No Charger, Nylon Pro Bag

By Burndy
Catalog # PAT644LILCBPB



PAT644 11T Dieless Latch Head Battery Crimper, No Batteries, No Charger, Nylon Pro Bag.

Features

- Dieless System with range taking capability
- #4 AWG -1000 kcmil Copper and Aluminum,#4 AWG - 556.5 kcmil ACSR, AAC, AAAC, ACAR
- 355° Rotatable latch head
- Audible pop-off indicates properly completed crimps
- Ergonomically balanced

Application

Crimping

General

| | |
|--------------------------|---|
| Application - For Use On | Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads |
| Battery Type | No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries) |
| Catalog Number | PAT644LILCBPB |
| Container Type | Nylon Pro Bag |
| Crimp Force Capacity | 11 ton |
| Die Type | Dieless |
| Power Source | No Charger |
| Tool Type | Battery Actuated Crimper |
| Trade Name | PATRIOT® |
| Type | Crimper |
| UPC | 621945561762 |
| UPC 12 Digit | 621945561762 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 15.62 in x 3.25 in x 14.12 in |
| Height | 14.12 in |

| | |
|--------|----------|
| Length | 15.62 in |
| Weight | 14.55 lb |
| Width | 3.25 in |

Electrical Ratings

| | |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

Conductor Related

| | |
|-----------------|---|
| Crimping Ranges | Copper: #4 AWG - 1000 kcmil; Copper Flex: #2 AWG - 777 kcmil; Aluminum: #6 AWG - 900 kcmil; ACSR #4 AWG - 556.5 kcmil |
|-----------------|---|

Certifications And Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | EX |
|------------------------------------|----|

Logistics

| | |
|-----------------------|------------------------------------|
| Carton Quantity | 1 |
| Minimum Pack Quantity | 1 |
| Package Contents | Crimper, Lanyard, Nylon Pro Bag |
| Pallet Quantity | 12 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50106125](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT644LILCBPB](#)

