



# PATRIOT® 12-Ton Covered C-Head Battery Crimper, Hydraulic Self-Contained, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy  
Catalog # [PAT750CLI](#)



PAT750 12T Covered C-Head Battery Crimper, 3Ah Li-ion, AC, Hard Case.

## Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

## Application

Crimping

## General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT750CLI
Container Type	Hard Case
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Power Source	120V-AC Charger
Recharge Time	0.5 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810508428
UPC 12 Digit	7818105084288

## Dimensions

Dimensions	15.75 in x 3.50 in x 13.50 in
Height	13.5 in
Jaw Width	1.65 in
Length	15.75 in
Weight	15.2 lb
Width	3.5 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground Rod: 1/2" - 1" diameter
-----------------	--

## Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 30001518](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Video - PAT750 Series](#)



A proud member of the Hubbell Family.

