



# PATRIOT® 12-Ton C-Head Battery Crimper, Hydraulic Self-Contained, No Batteries, No Charger, Hard Case

By Burndy  
Catalog # [PAT750LILCB](#)

PAT750 12T C-Head Battery Crimper, No Batteries, No Charger, Hard Case.

### Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

### Application

Crimping

### General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT750LILCB
Container Type	Hard Case
Crimp Force Capacity	12 ton
Die Type	U Die
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810540879
UPC 14 Digit GTIN	00781810540879

### Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Dimensions	15.75 in x 3.50 in x 13.50 in
Height	13.5 in
Jaw Width	1.65 in
Length	15.75 in
Weight	14.25 lb
Width	3.5 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground Rod: 1/2" - 1" diameter
-----------------	--

### Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Hard Case

### Product Assets

- [Brochures - PAT750 Series Brochure](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30001518](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT750LILCB](#)
- [Video - PAT750 Series](#)



A Hubbell brand