



**PATRIOT® 12-Ton C-Head Battery Crimper, Hydraulic Self-Contained, No Batteries, No Charger, Nylon Pro Bag**

By Burndy  
Catalog # [PAT750LILCBPB](#)

PAT750 12T C-Head Battery Crimper, No Batteries, No Charger, Nylon Pro Bag.

**Features**

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

**Application**

Crimping

**General**

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT750LILCBPB
Container Type	Nylon Pro Bag
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Contact Manufacturer
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561434

**Dimensions**

Dimensions	15.75 in x 3.50 in x 13.50 in
Height	13.5 in
Jaw Width	1.65 in



Length	15.75 in
Weight	14.25 lb
Width	3.5 in

**Electrical Ratings**

Operating Voltage	18 VDC
-------------------	--------

**Conductor Related**

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground Rod: 1/2" - 1" diameter
-----------------	--

**Certifications And Compliance**

Buy America(n) Qualified	Contact Manufacturer
Standards - RoHS Compliance	EX
Status	

**Logistics**

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Cutter, Lanyard, Nylon Pro Bag
Pallet Quantity	12

**Product Assets**

- [Brochures - PAT750 Series Brochure](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50106125](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT750LILCBPB](#)
- [Video - PAT750 Series](#)
- [Video - BURNDY Pro Bag, BURNDY Minute](#)