



PATRIOT® 4-POINT® 6-Ton Dieless Latch Head Battery Crimper, Guides, No Batteries, No Charger, No Case

By Burndy
Catalog # [PAT81K2U0000](#)



PAT81K2 4-POINT® 6T Dieless Latch Head Battery Crimper, Guides, No Batteries, No Charger, No Case

Features

- Dieless System with range taking capabilities
- 360° head rotation
- Unique crimping guides for improved reliability and ease of use
- Mechanical ram release (no battery consumption)
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	No Case/Bag
Crimp Force Capacity	6 ton
Die Type	Dieless
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC	621945645363
UPC 12 Digit	621945645363

Dimensions

Dimensions	15.2 in x 3.25 in x 14.93 in
Height	14.93 in
Length	15.2 in
Weight	11.05 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG -1000 kcmil; Copper Flex: #8 AWG - 777.7 kcmil; Aluminum: #8 AWG - 750 kcmil
-----------------	--

Logistics

Package Contents	Crimper, Lanyard
------------------	------------------

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Safety Operating & Maintenance Instructions - PATRIOT PAT81K@ Series Crimp Tools](#)
[Sales Drawings - 50123580](#)
[SDS - Burndy BAT18VLI SDS Sheet](#)
[Video - PATRIOT® 4-POINT® PAT81K2](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-PAT81K2U0000-SPEC-EN | REV 5/2023