



# PATRIOT® 4-POINT® 6-Ton Dieless Latch Head Battery Crimper, Guides, Pro Bag, No Batteries, No Charger

By Burndy  
Catalog # [PAT81K2U0003](#)



PAT81K2 4-POINT® 6T Dieless Latch Head Battery Crimper, Guides, Pro Bag, No Batteries, No Charger

## Features

- Dieless System with range taking capabilities
- 360° head rotation
- Unique crimping guides for improved reliability and ease of use
- Mechanical ram release (no battery consumption)
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Battery Type	No Batteries Included (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Nylon Pro Bag
Crimp Force Capacity	6 ton
Die Type	Dieless
Power Source	No Charger
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC	621945645387
UPC 12 Digit	621945645387

## Dimensions

Dimensions	15.2 in x 3.25 in x 14.93 in
Height	14.93 in
Length	15.2 in
Weight	11.05 lb
Width	3.25 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Copper: #8 AWG -1000 kcmil; Copper Flex: #8 AWG - 777.7 kcmil; Aluminum: #8 AWG - 750 kcmil
-----------------	--

## Logistics

Carton Quantity	1
Package Contents	Crimper, Lanyard, Nylon Pro Bag
Pallet Quantity	12

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Safety Operating & Maintenance Instructions - PATRIOT PAT81K@ Series Crimp Tools](#)
- [Sales Drawings - 50123580](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Video - PATRIOT® 4-POINT® PAT81K2](#)



A proud member of the Hubbell Family.